




DIOSPENTA™ 10 OPERATING GUIDELINES (65°)



* Chip Thinning Calculator is recommended to ensure hmax is greater than .003".

ISO	Materials			Vc Cutting Speed SFM	fz* Feed/Tooth (inch)	ap Recommended Axial Depth of Cut (inch)	Harder Tougher			Coolant
	Mat'l Group #VDI 3323	Type	Examples				IN2505	IN2530	IN2036	
P	1 thru 5	Non-alloy Steel	1018, A36, 1045, A572, 1070	400-1000	.004-.010	.060-.200	2	1		No
	6 thru 9	Low-alloy Steel	4140, 4340, P20, 8620, 300M	350-700						
	10, 11	High-alloy Steel	H13, A2, D2, M2, T1	300-600						
M	12 - 13	Stainless Steel (ferritic & martensitic)	410, 416, 440	350-600	.004-.009	.060-.200	3	2	1	Yes
	14	Stainless Steel (austenitic)	303, 304, 316, 15-5, 17-4	300-550						May not be required at high speeds
K	15 thru 16	Gray Cast Iron	CLS. 20, 30, 45	500-1000	.004-.010	.060-.200	1	2		No
	17 thru 20	Nodular Cast Iron	60-40-18, 100-70-03	400-800						
S	31 - 35	High-Temp Alloys	Inconel, Hastelloy, Nimonic, Monel	65-120	.004-.008	.060-.200	2	3	1	Yes
	36 - 37	Titanium Alloys	6Al-4V, 5Al-5Mo-5V-3Cr	85-130						

Note: Feed and speed recommendations are starting operating parameters. They are only guidelines from which further optimization should take place. Operating parameters are influenced by many machining variables. These variables may cause for reductions in feeds and speed or dramatic increases. Additionally, DOC and WOC may need to be revised to optimize the tools performance.